

# FlowCon SM 15-40mm

Dynamic Self Balancing Control Valve



#### **SPECIFICATIONS**

Pressure rating: Temperature rating, media: Temperature rating, ambient: Material:

- Diaphragm:
- Body:
- Union end connections:
- O-rings:


- Internal metal components: Body tappings : Maximum close off pressure: Maximum operational  $\Delta P$ : Flow rate range: 2500 kPa / 360 psi -20°C to +120°C / -4°F to +248°F -10°C to +50°C / +14°F to +122°F

Hydrogenated acrylonitrile-butadiene-rubber Forged brass ASTM CuZn40Pb2 Brass alloy ISO or NPT EPDM Stainless steel 1/4" NPT 600 kPa / 87 psi 320 kPaD / 46 psid 0.176-2.34 l/sec / 2.78-37.1 GPM


## DIMENSIONS AND WEIGHTS (NOMINAL) (measured in mm unless noted)

Model	Valve	L	H1	H2	H3	End connections C <sup>1</sup>			Weight <sup>2</sup> (kgs.)	Weight <sup>2</sup> (kgs.)	
no. size			with actuator SM.0.0.0.1		with actuator SM.0.0.0.3/4/5/6	ISO Female	ISO Male	Sweat	with actuator SM.0.0.0.1 (w/o end conn.)	with actuator SM.0.0.0.3/4/5/6 (w/o end conn.)	
	15					22	25	20			
SM.1.1	20	108	182	59	185	22	25	20	2.6	2,9	
	25					N/A	39	22			
	25					35	40	34			
SM.2.1	32	149	232	63	235	33	40	37	4.3	4.6	
	40					33	42	N/A	]		

Note 1: Add end connection length to body length. Note 2: Weight includes valve and actuators.




C



### **FLOW RATE TABLE**

Model	Valve size		Control range		Minimum setting			Maximum setting			Shut-off	
no.	mm	inch	kPaD	psid	l/sec	l/hr	GPM	l/sec	l/hr	GPM	leakage	
	15	1/2"	32-320	4.6-46	0.176	634	2.78	0.685	2470	10.9		
SM.1.1	20	3/4"									Leakage<0.05% of Kvs Kvs=4.1 m <sup>3</sup> /hr	
	25	1"										
	25	1"										
SM.2.1	32	1 1/4"	40-320	5.8-46	0.513	1850	8.13	2.34	8420	37.1	Leakage<0.05% of Kvs Kvs=12.6 m <sup>3</sup> /hr	
	40 1 1/2"										RV5-12.0 1117/11	



#### **MODEL NUMBER SELECTION**

			SM1	_··	•
ert body size: 5-25mm, 1/2"-1" <b>2=</b> 25-40m	m, 1"-1 1/2"				
ert dP control range: tandard					
ert p/t plug requirements: pressure/temperature plugs	P=taps plugged (standard) —				
ert actuator selection:					
rush/basic (standard, SM.0.0.	0.1) <b>3</b> =display (SM.0.0.0.3) 5) <b>6</b> =display, BACnet and fa nections:	<b>4</b> =display and failsafe (SM.0 iilsafe (SM.0.0.0.6)	0.0.0.4)		
rush/basic (standard, SM.0.0. lisplay and BACnet (SM.0.0.0.	5) 6=display, BACnet and fa	<b>4</b> =display and failsafe (SM.0 iilsafe (SM.0.0.0.6) Male treaded	0.0.0.4)		
rush/basic (standard, SM.0.0. lisplay and BACnet (SM.0.0.0 ert inlet x outlet union end con	5) <b>6</b> =display, BACnet and fa nections:	illsafe (SM.0.0.0.6)			


I=ISO N=NPT

Example: SM.2.1.B.1.Q.Q.I=SM 25-40mm body with p/t plugs, standard brush basic actuator and 40mm ISO female threaded end connections.

### **ACTUATOR SPECIFICATIONS<sup>3</sup>**

#### FlowCon SM.0.0.1 actuator

Supply voltage: Power consumption: Frequency: Control input: Feedback position output: Turn time: Electrical connection: Direction of rotation: Humidity rating: Housing material: Housing insulation: 24V AC or 30V DC 20VA @ 26V AC 50/60 HZ 2-10V DC, 4-20mA or 3-point floating 2-10V DC or 4-20mA 150 seconds (from closed to fully open valve) 15mm grommet connection Bi-directional Fully coated electronic board Aluminium IP42



#### FlowCon SM.0.0.0.3, SM.0.0.0.4, SM.0.0.0.5 (with BACnet) and SM.0.0.0.6 (with BACnet and failsafe) actuators 24V AC/DC Supply voltage: Power consumption: 12VA 50/60 HZ Frequency: 0-10V DC, 2-10V DC, 0-20mA, 4-20mA, Control input: 2-position or 3-point floating Feedback position output: Automatic match of control input, 0-10V DC, 2-10V DC or 4-20mA Turn time: 190 seconds (from closed to fully open valve) Electrical connection: 5 wires 22 AWG halogen free cable, 1 meter For BACnet versions another 3 wires 22 AWG halogen free cable, 1 meter Direction of rotation: **Bi-directional** Humidity rating: 5 to 95% RH non condensing Housing material: UL94 V0-rated plastic IP54 including up-side-down mounting Housing insulation: External programming of all settings, interface of buttons and display Programming: Calibration: Automatic calibration at startup Valve - actuator coupling: Easy snap coupling BACnet device profile: BACnet Application Specific Controller (B-ASC) type server BACnet Master Slave/Token passing (MS/TP) BACnet protocol: 9600, 19200, 38400 and 76800 BACnet baud rates supported:


BACnet services (BIBBS) supported: DS-RP-B, DS-WP-B, DM-DDB-B, DM-DOB-B and DM-DCC-B.

Note 3: FlowCon warranty is voided using other actuators than supplied or recommended by FlowCon International A/S.

### FLOW RATE SETTING - VALVE SIZE DN15-DN40

	•	huximum	Flow Rate				
DN15	-DN25 · 1	/2"-1"	DN25-DN40 · 1"-1 1/2" 40-320 kPaD · 5.8-46 psid SM.2.1				
32-320	(PaD · 4.6	-46 psid					
	SM.1.1						
l/sec l/hr		GPM	l/sec	l/hr	GPM		
0.176	633	2.78	0.513	1850	8.13		
0.195	702	3.09	0.573	2060	9.08		
		3.39	0.632	2280	10.0		
0.214 770 0.233 838		3.69	0.690	2480	10.0		
0.251	902	3.97	0.746	2690	11.8		
0.268	964	4.24	0.802	2890	12.7		
).285	1030	4.51	0.856	3080	13.6		
.205	1030	4.77	0.830	3270	14.4		
).317	1140		0.909	3460	14.4		
		5.02					
0.332	1200	5.26	1.01	3640	16.0		
).347	1250	5.50	1.06	3820	16.8		
0.362	1300	5.73	1.11	4000	17.6		
0.376	1350	5.96	1.16	4170	18.3		
0.390	1400	6.18	1.20	4330	19.1		
0.403	1450	6.38	1.25	4500	19.8		
).416	1500	6.59	1.29	4660	20.5		
).428	1540	6.78	1.34	4810	21.2		
).440	1580	6.97	1.38	4970	21.9		
).452	1630	7.16	1.42	5120	22.5		
.463	1670	7.33	1.46	5260	23.2		
).474	1710	7.51	1.50	5400	23.8		
.485	1750	7.68	1.54	5540	24.4		
.495	1780	7.84	1.58	5680	25.0		
.505	1820	8.00	1.61	5810	25.6		
.515	1850	8.16	1.65	5940	26.2		
).524	1890	8.30	1.69	6070	26.7		
.533	1920	8.44	1.72	6190	27.3		
.542	1950	8.59	1.75	6310	27.8		
.550	1980	8.71	1.79	6430	28.3		
).559	2010	8.86	1.82	6550	28.8		
).567	2040	8.98	1.85	6660	29.3		
).574	2070	9.09	1.88	6770	29.8		
).582	2100	9.22	1.91	6870	30.3		
).589	2120	9.33	1.94	6980	30.7		
).596	2120	9.44	1.97	7080	31.2		
0.603	2170	9.55	1.99	7180	31.6		
0.609	2190	9.66	2.02	7280	32.0		
).616	2220	9.76	2.02	7370	32.5		
).622	2240	9.85	2.03	7460	32.9		
).628	2240	9.95	2.07	7400	33.3		
0.634	2280	10.1	2.10	7640	33.6		
).634 ).639			2.12				
	2300	10.1 10.2		7730	34.0		
0.645	2320		2.17	7810	34.4		
0.650	2340	10.3	2.19	7890	34.8		
0.655	2360	10.4	2.22	7970	35.1		
0.661	2380	10.5	2.24	8050	35.5		
0.667	2400	10.6	2.26	8130	35.8		
).671	2420	10.6	2.28	8200	36.1		
0.676	2430	10.7	2.30	8280	36.4		
0.680	2450	10.8	2.32	8350	36.8		
.685	2470	10.9	2.34	8420	37.1		

	Maxir DIP S		Stem Rotations From Closed								
Used on SM.0.0.1											
1	2	3	4	5	6	Rotations					
ON	ON	ON	ON	ON	ON	1.0					
OFF	ON	ON	ON	ON	ON	1.1					
ON	OFF	ON	ON	ON	ON	1.2					
OFF	OFF	ON	ON	ON	ON	1.3					
ON	ON	OFF	ON	ON	ON	1.4					
OFF	ON	OFF	ON	ON	ON	1.5					
ON	OFF	OFF	ON	ON	ON	1.6					
OFF	OFF	OFF	ON	ON	ON	1.7					
ON	ON	ON	OFF	ON	ON	1.8					
OFF	ON	ON	OFF	ON	ON	1.9					
ON	OFF	ON	OFF	ON	ON	2.0					
OFF	OFF	ON	OFF	ON	ON	2.1					
ON	ON	<u> </u>	OFF	ON	ON	2.2					
OFF	ON	OFF	OFF	ON	ON	2.3					
ON OFF	OFF OFF	OFF OFF	OFF OFF	ON ON	ON ON	2.4					
OFF	OFF	OFF	OFF	OFF	ON	2.5					
OFF	ON	ON	ON	OFF	ON	2.0					
ON	OFF	ON	ON	OFF	ON	2.8					
OFF	OFF	ON	ON	OFF	ON	2.9					
ON	ON	OFF	ON	OFF	ON	3.0					
OFF	ON	OFF	ON	OFF	ON	3.1					
	_	OFF	ON	OFF	ON	3.2					
OFF	OFF	OFF	ON	OFF	ON	3.3					
ON	ON	ON	OFF	OFF	ON	3.4					
OFF	ON	ON	OFF	OFF	ON	3.5					
ON	OFF	ON	OFF	OFF	ON	3.6					
OFF	OFF	ON	OFF	OFF	ON	3.7					
ON	ON	OFF	OFF	OFF	ON	3.8					
OFF	ON	OFF	OFF	OFF	ON	3.9					
ON	OFF	OFF	OFF	OFF	ON	4.0					
OFF	OFF	OFF	OFF	OFF	ON	4.1					
ON	ON	ON	ON	ON	OFF	4.2					
OFF	ON	ON	ON	ON	OFF	4.3					
	OFF		ON	ON	OFF	4.4					
	OFF	ON	ON	ON	OFF	4.5					
ON		OFF		ON	OFF	4.6					
OFF	_	OFF	ON	ON	OFF	4.7					
		OFF	ON	ON	OFF	4.8					
	OFF	OFF	ON	ON	OFF	4.9					
ON OFF	ON	ON	OFF	ON	OFF	5.0					
	ON OFF	ON	OFF	ON	OFF	5.1					
OFF	OFF	ON ON	OFF OFF	ON ON	OFF OFF	5.2 5.3					
OFF	OFF		OFF	ON	OFF	5.3					
OFF	ON	· · · · · · · · · · · · · · · · · · ·	OFF	ON	OFF	5.5					
	OFF			ON	OFF	5.6					
	OFF		OFF	ON	OFF	5.7					
ON	ON	ON	ON	_	OFF	5.8					
OFF		ON	ON		OFF	5.9					
ON	OFF	ON	ON		OFF	6.0					



Example illustrated above:

#### ON-OFF-ON-ON-OFF-OFF

which gives a max flow of:

**SM.1.1** - 0.685 l/sec and **SM.2.1** - 2.34 l/sec (rotation 6.0).

Accuracy: Greatest of either  $\pm 5\%$  of controlled flow rate or  $\pm 2\%$  of maximum flow rate.

#### **GENERAL DESCRIPTION**

The SM Series are self balancing dynamic flow control valves that are pressure independent, two-way, modulating to accept digital or analog input signals. The valves accept 2-10V DC, 4-20mA or digital 3-point floating input signals. Each valve has an adjustable maximum flow rate setting to enable flow limitation and balancing to the coils or zones that the valves are controlling.

All SM actuators are microprocessor based with a self-calibrating feature. The valves are all designed for double union piping connection. They are available in two different valve bodies with end connections from 15mm-40mm.

#### **GENERAL SPECIFICATIONS**

#### 1. PRESSURE INDEPENDENT DYNAMIC CONTROL VALVES - FLOWCON SM

- 1.1. Contractor shall install pressure independent dynamic control valves where indicated in drawings.
- 1.2. Valve shall be an electronic, dynamic, modulating, 2-way pressure independent control device.
- 1.3. Pressure independent dynamic control valve shall accurately control flow, independent of system pressure fluctuation.
- 1.4. Maximum flow setting shall be adjustable to 51 different settings within the range of the valve size.

#### 2.a. VALVE ACTUATOR / FLOWCON SM.0.0.1

- 2.a.1. Valve actuator housing shall be rated to IP42.
- 2.a.2. Actuator shall be driven by a 24V AC or 30V DC motor, and shall accept 2-10V DC, 4-20mA or 3-point floating electric signal and shall include resistor to facilitate any of these signals.
- 2.a.3. Actuator shall be capable of providing 4-20mA or 2-10V DC feedback signal to the control system.
- 2.a.4. External LED read-out of current valve position and maximum valve position setting shall be available.

#### 0R...

#### 2.b. VALVE ACTUATOR / FLOWCON SM.0.0.0.3, SM.0.0.0.4, SM.0.0.0.5 and SM.0.0.0.6

- 2.b.1. Valve and actuator coupling shall have snap couplings for fast mounting and demounting.
- 2.b.2. Actuator housing shall be rated to IP54 including up-side-down mounting.
- 2.b.3. Actuator shall be driven by a 24V AC/DC motor and shall accept 0-10V DC, 2-10V DC, 0-20mA, 4-20mA, 2-position or 3-point floating electric input signal.
- 2.b.4. Actuator shall be capable of providing same as input, 4-20mA, 0-10V DC or 2-10V DC feedback signal to the control system.
- 2.b.5. Automatic calibration of valve position shall be standard.
- 2.b.6. Actuator shall include display and buttons for external programming of all settings.
- 2.b.7. External display of current valve flow, maximum valve flow, input signal, feedback signal and operational direction shall be standard.
- 2.b.8. Optional fail safe system to power valve to either open (max. setting) or closed position from any position in case of power failure shall be available.
- 2.b.9. Optional BACnet connection for remote setting and control of actuator shall be available.


#### 3. VALVE HOUSING

- 3.1. Valve housing shall consist of forged brass ASTM CuZn40Pb2, rated at no less than 2500 kPa static pressure and +120°C.
- 3.2. Valve housing shall be permanently marked to show direction of flow.
- 3.3. Valve housing shall be double union end constructed with a range of pipe connections available for the appropriate pipe size.
- 3.4. Optional dual pressure/temperature test plugs for verifying accuracy of flow performance shall be available for all valve sizes.

#### 4. FLOW REGULATOR / AUTOMATIC BALANCING UNIT

- 4.1. Flow regulation unit shall be manufactured of stainless steel and hydrogenated acrylonitrilebutadiene-rubber and shall be capable of controlling flow within ±5% rated flow rate or ±2% of maximum flow rate.
- 4.2. Flow regulation unit shall be accessible for change-out maintenance.

### **APPLICATION AND SCHEMATIC EXAMPLE**



### **UPDATES**

#### For latest updates please see www.flowcon.com

FlowCon International can accept no responsibility for possible errors in any printed material. All rights reserved.